



GE
Lighting

28089 - GE LED Bright Stik™

LED10LS3/828

Product Photo



GENERAL CHARACTERISTICS

Product Technology	LED
Rated Life (Hours)	15000 h
Base	E26

PHOTOMETRIC CHARACTERISTICS

Beam Spread (range)	0 deg
Lumens per Watt (Efficacy)	76 lm
Initial Lumens-nominal	760 lm
Color Rendering Index-CRI	80
Color Temperature	2850 K

PRODUCT INFORMATION

Product Code	28089
Description	LED10LS3/828
Alternative Unit Of Measure	EACH
Standard Package Quantity	16
Ean UPC	043168280891
Standard Package GTIN	00043168280891
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	16
Sales Unit	Each
UCC	043168280891
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168280891
Standard Package GTIN	10043168280898
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168280891

DIMENSIONS

Bulb Max Overall Length-MOL	4.45 in
-----------------------------	---------

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Input Voltage [nom]	120 W