



GE
Lighting

92967 - GE LED PAR38 - Low Glare - Visual Comfort Lens™

LED18D38OW383040

Product Photo



GENERAL CHARACTERISTICS

Product Technology	LED
Rated Life (Hours)	25000 h
Base	E26

PHOTOMETRIC CHARACTERISTICS

Beam Spread (range)	40 deg
Center Beam Candle Pwr Candela	4000 cd
Nominal Initial Lumen per Watt	86.1
Rated Beam Spread	40 deg
Initial Lumens-nominal	1550 lm
Color Rendering Index-CRI	81
Color Temperature	3000 K

PRODUCT INFORMATION

Product Code	92967
Description	LED18D38OW383040
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168929677
Standard Package GTIN	00043168929677
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168929677
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168929677
Standard Package GTIN	10043168929674
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168929677

DIMENSIONS

Bulb Max Overall Length-MOL	5.12 in
-----------------------------	---------

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Input Voltage [nom]	120 V