



Catamount®

T&B Catalog Number: L-11-40-0-C
UPC Number: 72849493301
Description: Cable Tie 40lb 11" Ultraviolet Resistant Black All-Nylon 100 Per Bag

Status: Active

General	
Material	Nylon 6.6 Weather Resistant
Color	Black
Dimension Information	
Length (inches)	11.5
Width (inches)	0.146
Max. Wire Bundle Diameter (inches)	3
Min. Wire Bundle Diameter (inches)	1/16
Specifications	
Tensile Strength (lbs.)	40
Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2
Tooling	
Application Tools	ERG50, QC-100, L-200, L-400-C
Packaging	
T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	5000
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	3.61 lbs. per 1000
Application Support	
T&B Sales Drawings	wsd-000221
Overview	Available on Website
Material Selection Guide	Available on Website
Available Colors	Available on Website
Certifications	
RoHS Compliance	Yes



For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com