



Hoffman

Lay-In NEMA Type 12 Wireway Straight Section

Catalog Number: F66L120
US List Price (USD): \$550.00

Bulletin Number:

- F10

Material:

- Steel



Model Code:

- 18540

Ship Wt. Std. Pkg. (lbs):

- 73.0

Interchangeable:

- False

IP Rating:

- IP54

Description

Available in lengths from 6.00 in. (152 mm) to 120.00 in. (3048 mm).

Description:

Available in lengths from 6.00 in. (152 mm) to 120.00 in. (3048 mm).

Notes:

- Each sealing plate also includes one gasket and one set of screws to join sections.
- Certified by Canadian Standards Association.

Technical Data

Lay-In NEMA Type 12 Wireway Straight Section

Catalog Number	F66L120
A in.	6
B in.	6
C in.	120
D in.	7.62
E in.	7.62
Sealing Plates Type	Flat
Sealing Plates Qty.	1

Certifications



UL Certification

Documents



3D STEP CAD



2D DXF CAD



Spec Sheet



DOC



Dimension Drawing

No accessories available.