

Rittal – The System.

Faster – better – everywhere.

▶ Junction boxes JB Stainless steel – JB 8018.139

Date : Oct 29, 2015

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Junction boxes JB Stainless steel – JB 8018.139 - JB121008H4

created : 29.10.2015 build on www.rittal.com/us-en



Product description

Material: Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal
Housing: Stainless steel 1.4301 (AISI 304)

Surface finish: Housing and door: Brushed, grain 240

**Protection category
IP to IEC 60 529:** IP 66

**Protection category
NEMA:** NEMA 4X

Supply includes: 180° hinge
Mounting plate

Packaging unit: 1 pc(s).

Product features

Dimensions: Height: 300 mm (12 ")
Width: 250 mm (9.8 ")
Depth: 200 mm (7.9 ")

Material thickness: Housing: 1.5 mm (0.06 ")
Door: 1.5 mm (0.06 ")

Door catch: left


Weight/pack: 5 kg (11 lb.)

Approvals

Approvals:  [Approvals \(US\)](#)

Downloads

Data sheets: [Graphics \(US\)](#)

Documentation:  [Info sheet \(US\)](#)
 [Load brochure \(US\)](#)

CAD drawings: [Request](#)