



GE
Lighting

92963 - null

LED18D380W383025

Product Photo



GENERAL CHARACTERISTICS

Product Technology	LED
Rated Life (Hours)	25000 h
Base	E26

PHOTOMETRIC CHARACTERISTICS

Beam Spread (range)	25 deg
Center Beam Candle Pwr Candela	6000 cd
Nominal Initial Lumen per Watt	86.1
Rated Beam Spread	25 deg
Initial Lumens-nominal	1550 lm
Color Rendering Index-CRI	81
Color Temperature	3000 K

PRODUCT INFORMATION

Product Code	92963
Description	LED18D380W383025
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168929639
Standard Package GTIN	00043168929639
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168929639
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168929639
Standard Package GTIN	10043168929636
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168929639

DIMENSIONS

Bulb Max Overall Length-MOL	5.12 in
-----------------------------	---------

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Input Voltage [nom]	120 V