



*Hoffman*

## Lay-In NEMA Type 1 Galvanized Wireway Straight Section

Catalog Number: F44T124GV  
US List Price (USD): \$25.59

### Bulletin Number:

- F40G

### Material:

- Steel



### Model Code:

- 88140

### Ship Wt. Std. Pkg. (lbs):

- 29.2

### Interchangeable:

- False

## Description

---

### Description:

Available in lengths from 12.00 in. (305 mm) to 120.00 in. (3048 mm), with or without knockouts.

## Technical Data

---

### Lay-In NEMA Type 1 Galvanized Wireway Straight Section

<b>Catalog Number</b>	<a href="#">F44T124GV</a>
<b>A in.</b>	4
<b>B in.</b>	4
<b>C in.</b>	24
<b>F in.</b>	---
<b>X in.</b>	---
<b>Y in.</b>	---
<b>Number of Knockouts .50 in.-.75 in.</b>	—
<b>Number of Knockouts 1.00 in.-1.25 in.</b>	---

## Certifications

---



EU Certification



UL Certification

## Documents

---



Spec Sheet



2D DXF CAD



3D STEP CAD



Dimension Drawing

No accessories available.