

# 12V LED 6.5W 35 Deg FL Well 30K BBR

16034BBR30 (Bronzed Brass)

Project Name: \_\_\_\_\_  
Location: \_\_\_\_\_  
Type: \_\_\_\_\_  
Qty: \_\_\_\_\_  
Comments: \_\_\_\_\_

## Ordering Information

|                    |               |
|--------------------|---------------|
| Product ID         | 16034BBR30    |
| Finish             | Bronzed Brass |
| Available Finishes | BBR, BBR      |

## Dimensions

|        |          |
|--------|----------|
| Weight | 4.00 LBS |
|--------|----------|

## Photometrics

|                       |       |
|-----------------------|-------|
| Kelvin Temperature    | 3000K |
| Color Rendering Index | 80    |

## Specifications

|                   |                      |
|-------------------|----------------------|
| Material          | Brass                |
| Glass Description | 35 Beam Spread Optic |

## Electrical

|                         |                |
|-------------------------|----------------|
| Voltage                 | 12V            |
| Operating Voltage Range | 9 - 15 VAC/VDC |

## Qualifications

|                    |  |
|--------------------|--|
| Safety Rated       | Wet  |
| Expected Life Span | 400000 Hours   |
| Warranty           | <a href="http://www.kichler.com/warranty">www.kichler.com/warranty</a> |

## Primary Lamping

|                       |            |
|-----------------------|------------|
| Light Source          | LED        |
| Lamp Included         | Integrated |
| Number of Lights/LEDs | 5          |
| Max or Nominal Watt   | 6.4W       |



## Dimensions

|        |        |
|--------|--------|
| Height | 11.00" |
| Length | 6.50"  |
| Width  | 6.50"  |

### Notes:

- 1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
- 2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.