



Hoffman

Wiring Trough, NEMA Type 3R

Catalog Number: A8872RT
US List Price (USD): \$404.30

Bulletin Number:

- F40PT

Material:

- Steel



Model Code:

- 42999

Ship Wt. Std. Pkg. (lbs):

- 60.0

Interchangeable:

- False

IP Rating:

- IP32

Industry Standards:

UL 870 Listed; File No. E27524; Raintight cUL CSA C22.2 No. 26 Listed; File No. E27524; Raintight NEMA/EEMAC Type 3R IEC 60529, IP32

Description

Available in a range of sizes, this wiring trough meets basic functionality requirements for applications subjected to moisture.

Applications:

Available in a range of sizes, this wiring trough meets basic functionality requirements for applications subjected to moisture.

Features:

- Drip shield top and seam-free sides, front, and back
- Slip-on removable cover
- Embossed mounting holes on back of enclosure
- Provision for padlocking
- No gasketing or knockouts

Finish:

ANSI 61 gray polyester powder paint finish inside and out over pretreated surfaces.

Specifications:

16 or 14 gauge plated steel

Accessories:

Touch-Up Paint (ATPPY61)

Technical Data

Wiring Trough, NEMA Type 3R

Catalog Number	A8872RT
A in.	8
B in.	8
C in.	72
Gauge	14

Certifications



EU Certification



EU Certification

Documents



Spec Sheet



2D DXF CAD



3D STEP CAD



DOC



Dimension Drawing

No accessories available.