



Hoffman

Screw-Cover, Type 3R

Catalog Number: A24R188NK
US List Price (USD): \$203.30

Bulletin Number:

- A90S3

Finish:

- ANSI 61

Material:

- Steel



Model Code:

- 13517

Ship Wt. Std. Pkg. (lbs):

- 32.0

Interchangeable:

- False

Finish:

- Galv/paint

Industry Standards:

UL 50, 50E Listed; Type 3R; File No. E27525 cUL Listed per CSA C22.2 No 94;
Type 3R; File No. E27525 NEMA/EEMAC Type 3R IEC 60529, IP32

Description

Use this enclosure with or without knockouts in outdoor applications as a wiring or junction box.

Application:

Use this enclosure with or without knockouts in outdoor applications as a wiring or junction box.

Features:

- Drip shield top and seam-free sides, front and back
- Slip-on removable cover fastened with plated steel screws along bottom edge
- Handles on larger sizes (see table)
- Embossed mounting holes on back of enclosure
- Knockouts in bottom of 16 and 14 gauge enclosures
- Provision for padlocking
- No gasketing

Specifications:

16, 14 or 12 gauge galvanized steel

Finish:

ANSI 61 gray polyester powder paint finish inside and out over pretreated surfaces.

Accessories:

- Industrial Corrosion Inhibitors
- Electric Heater
- Grounding Device
- Mounting Bracket Kit
- Touch-Up Paint

Technical Data

Screw-Cover, Type 3R

Catalog Number	A24R188NK
A in.	24
B in.	18
C in.	8
D in.	—
Mounting H in.	13.00
Body Style	B
Mounting J in.	1.12

Certifications



UL Certification



EU Certification

Documents



Spec Sheet



3D STEP CAD



2D DXF CAD



Dimension Drawing

Accessories

Item		
	Mounting Bracket Kit	AMFK3RL014
	Grounding Device	AGS816
	Grounding Device	AGLK2
	Grounding Device	AGS408
	Grounding Device	AGS416
	Grounding Device	AGS808
	Touch-Up Paint	ATPPY61