

CRAFTMADE

Titan - TIT52SCH5LKRCI

52" Ceiling Fan with Blades and Light



Offering a modern twist on classic ceiling fan design, the Titan satisfies with efficient air movement, inviting overhead lighting, and striking contemporary form. The Titan offers efficiency to match its design-forward style, moving far more air on far less energy.

- 3-Speed Reversible Motor
- 6" Downrod (Included)
- Reversible Glossy Black/White Pine Blades (Included)
- Integrated Light Kit (1-100 Watt E11 Halogen Bulb Included)
- RCI-104 Remote Control (Included)
- Tri-Mount = (Flat or sloped ceiling downrod mount, or semi-flushmount)


Specs

Blade Sweep Opt (in.)	52
Blades	5
Blade Pitch (°)	13
Motor Size (MM)	172 x 16
Amps at High Speed	2

Airflow (CFM)	5033
Watts (Hi Speed)	63
Efficiency (CFM/Watt)	80
Shipping Weight (lbs.)	23.81
Carton Size (CU FT)	2.05
Bulb Wattage	100
Finish	Satin Chrome

Dimensions

A:	16.75"
B:	13.07"
C:	12.25"
D:	5.12"
E:	6.25"
H:	5.12"
I:	6.25"
Downrod Length (in.)	6"



Guide

Titan - TIT52SCH5LKRCI



[Installation Guide](#)

Craftmade • P.O. Box 1037 • Coppel, TX 75019 • [Privacy Policy](#) • [Site Map](#) • © 2017 All Rights Reserved