

Product Datasheet

[Catalog Home](#)
[Home Page](#)
[Search](#)



GF20ILA -- Circuit Guard LED GFCI Receptacle



20A 125V AC, LED Series

20A 125V, 2P 3W, Flush Thermoplastic Face, Back & Side Wired, Matching Wall Plate Included, Ivory

Product Specifications

GFCI Product Type	 Receptacles
Receptacle Version	LED Indicator Series Receptacle
Receptacle Grade	Commercial
Wiring Style	Internal Backwire
Amperage	20A
Color	 Ivory
Voltage	125V AC
Packaging	Single
Trip Level	4-6 mA
Trip Time	0.025 seconds
Frequency	60Hz
Voltage Range	120V AC +10% -15%
Amperage Range	15A/20A, 20 Amps Feed Thru
Max Humidity	0.95
Max Interrupting Capacity	10,000 Amps
Operating Temp	Deg F -30 to 150 (Deg C -30 to 66)
Codes and Standards	Meets UL 943 Class A GFCIs and UL 498 for Receptacles. Complies to NEC, CEC & OSHA. UL File E-41978, CSA File LR-24886
Terminal Accommodations	#14 -10 AWG stranded or solid copper conductors only.
Note:	GFCI Receptacles should not be used in critical care patient areas or for electrical life support equipment.
UPC Number	88377837910
Weight in LBs	0.3

Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog
