



*Hoffman*

## Wiring Trough, NEMA Type 3R

Catalog Number: A6672RT  
US List Price (USD): \$252.70

### Bulletin Number:

- F40PT

### Material:

- Steel



### Model Code:

- 38310

### Ship Wt. Std. Pkg. (lbs):

- 35.7

### Interchangeable:

- False

### IP Rating:

- IP32

### Industry Standards:

UL 870 Listed; File No. E27524; Raintight cUL CSA C22.2 No. 26 Listed; File No. E27524; Raintight NEMA/EEMAC Type 3R IEC 60529, IP32

## Description

---

Available in a range of sizes, this wiring trough meets basic functionality requirements for applications subjected to moisture.

### Applications:

Available in a range of sizes, this wiring trough meets basic functionality requirements for applications subjected to moisture.

### Features:

- Drip shield top and seam-free sides, front, and back
- Slip-on removable cover
- Embossed mounting holes on back of enclosure
- Provision for padlocking
- No gasketing or knockouts

### Finish:

ANSI 61 gray polyester powder paint finish inside and out over pretreated surfaces.

**Specifications:**

16 or 14 gauge plated steel

**Accessories:**

Touch-Up Paint (ATPPY61)

## Technical Data

---

### Wiring Trough, NEMA Type 3R

<b>Catalog Number</b>	<a href="#">A6672RT</a>
<b>A in.</b>	6
<b>B in.</b>	6
<b>C in.</b>	72
<b>Gauge</b>	16

## Certifications

---



EU Certification



EU Certification

## Documents

---



Spec Sheet



2D DXF CAD



3D STEP CAD



DOC



Dimension Drawing

No accessories available.