

P1307ORB: 1 - Light Tabby Pendant



Dimensions:

Diameter: 12" **Overall Height:** 81"
Height: 15 7/8" **Wire:** 160" (color/Brown)
Weight: 7.04 lbs. **Chain:** 60"
Connection: Mounted To Box

Bulbs:

1 - Medium 60w Max. 120v - Not included

Features:

•

Material List:

1 Body - Metal & Glass - Oil Rubbed Bronze

Safety Listing:

Safety Listed for Damp Locations / Non-IC

Instruction Sheets:

Trilingual (English, Spanish, and French) (P1307-P1308-P1317-P1318)
 Trilingual (English, Spanish, and French) (P1307ORB)

Collection: Tabby

Medium Base Squirrel Cage Antique Bulb Recommended

UPC #: 014817524611

Finish: Oil Rubbed Bronze (ORB)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Clear	1				10 7/8	12				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	7/8			5 1/2		

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship

Feiss reserves the right to revise the design of components of any product due to parts availability or change in safety listing standards without assuming any obligation or liability to modify any products previously manufactured and without notice. This literature depicts a product design that is the sole and exclusive property of Feiss. In compliance with U.S copyright and patent requirements, notification is hereby presented in this form that this literature, or the product it depicts, is not to be copied, altered or used in any manner without the express written consent of, or contrary to the best interests of Feiss 1/2 A Generation Brands Company.

Individual	P1307ORB	1	014817524611	13.38	11.75	11.58	1.054	5.2	150	Yes
NJ Pallet		24		48	40	74.5	82.778	436.8		No
NV Pallet		24		48	40	68.5	76.111	206.4		No