

**Canfield Patio Collection**  
**52 Inch Canfield Patio Fan WH**  
 310192WH (White)

Project Name: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Qty: \_\_\_\_\_  
 Comments: \_\_\_\_\_

**Product Information**

Product ID	310192WH
Finish	White
Blade Finish	White/White
Collection	Canfield Patio Collection

**Airflow, Power and Efficiency**

Speed	RPM	CFM	CFM/ Watt	Amps	Watts
High	186	6338	92	.5	69
Med	129	4520	133	.42	34
Low	58	2363	236	.23	10

**Specifications**

Number of Blades	5
Blades Included	Yes
Blade Pitch	14 Degrees
Blade Sweep	52"
Blades Reversible	No
Blade Material	ABS
Optional Blades Available	No
Downrod 1	1.00 OD X 4.00

Primary Control System  
 Pull Chain - In project applications using multiple ceiling fans, alternative remote controls may be required. Please contact Kichler Advanced Product Solutions at 844-542-4537 to confirm your project requirements.

Remote Included	No
Wall Control Included	No
Low Ceiling Adaptable	Yes, With Optional Flush Mount
Lead Wire Length	78.00"
Motor Size	172MM X 20MM
Motor Type	AC


**Downlight**

Watts	69/34/10
Optional Light Kit Available	No

**Safety Listings & Certifications**



**Dimensions**



Downrod	A	B	C	D
1.00 OD X 4.00	13.25	11.00	12.60	6.25

**Available Finishes**

Finish	Fixture	Glass	Blade 1	Blade 2

# Canfield Patio Collection

## 52 Inch Canfield Patio Fan WH

310192WH (White)

Project Name: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Qty: \_\_\_\_\_  
 Comments: \_\_\_\_\_

Finish	Fixture	Glass	Blade 1	Blade 2
Tannery Bronze Powder Coat	310192TZP	NONE	CHERRY	WALNUT
Weathered Steel Powder Coat	310192WSP	NONE	TEAK	WALNUT
Weathered Copper Powder Coat	310192WCP	NONE	MEDIUM WALNUT	DARK WALNUT
Satin Natural Black	310192SBK		SATIN NATURAL BLACK	SATIN BLACK
White	310192WH		WHITE	WHITE

Safety Rated	Portable Wet
Energy Star	Yes
Warranty	www.kichler.com/warranty

### Installation

Installation requirements

The electrical junction box and support structure must be securely mounted and capable of reliably supporting a minimum of 50 pounds. Use only ETL/UL listed electrical junction boxes marked ""For Fan Support""

Electrical Requirements	120V 60Hz AC
Hanging Weight	24.2 LBS
Minimum Distance Between Bottom Of Fan Blade To Floor	7.5 feet

### Control Options

Product ID	Descr
337214	Limited Function Cooltouch
370039MUL	Wall Control System L-Function
3W500SBK	CoolTouch Control System W500