



GE  
Lighting

92958 - null

LED18D380W382740

Product Photo



#### GENERAL CHARACTERISTICS

Product Technology	LED
Rated Life (Hours)	25000 h
Base	E26

#### PHOTOMETRIC CHARACTERISTICS

Beam Spread (range)	40 deg
Center Beam Candle Pwr Candela	3800 cd
Nominal Initial Lumen per Watt	86.1
Rated Beam Spread	40 deg
Initial Lumens-nominal	1550 lm
Color Rendering Index-CRI	81
Color Temperature	2700 K

#### PRODUCT INFORMATION

Product Code	92958
Description	LED18D380W382740
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168929585
Standard Package GTIN	10043168929582
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168929585
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168929585
Standard Package GTIN	00043168929585
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168929585

#### DIMENSIONS

Bulb Max Overall Length-MOL	5.12 in
-----------------------------	---------

#### ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Input Voltage [nom]	120 V