



BR/R LED

9BR30/LED/827/DIM 120V

Philips BR Dimmable LED Lamps with AirFlux technology provide a soft, diffused level of light and smooth dimming to reduce glare. The sleek, lightweight design is ideal for downlighting.

Product data


General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Bulb Shape	BR30 (BR30)
Nominal Lifetime (Nom)	10000 h
Switching Cycle	50000X
Technical Type	9-65W
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux (Nom)	650 lm
Luminous Flux (Rated) (Nom)	650 lm
Color Designation	Soft White
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	73 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	9 W
Lamp Current (Nom)	95 mA
Wattage Equivalent	65 W

Starting Time (Nom)	0.5 s
Warm Up Time To 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.8
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	76 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	9 kWh
Product Data	
Order product name	9BR30/LED/827/DIM 120V
EAN/UPC - Product	046677458102
Order code	929001174966
Numerator - Quantity Per Pack	1

BR/R LED

Numerator - Packs per outer box	6
Material Nr. (12NC)	929001174966
Net Weight (Piece)	0.064 kg

Dimensional drawing



Basic BR30 120V 9W-65W 650lm 2700K E26 D

Product	D	C
9BR30/LED/827/DIM 120V	96 mm	132 mm

Photometric data

Accent Lighting - Spots

