



LUNA LED STEP 12V 15508BZ	
BRONZE	

WIDTH:	4.5"
HEIGHT:	3.0"
WEIGHT:	0.7 LBS
MATERIAL:	ZINC-ALUMINUM ALLOY
SOCKET:	3.80W LED *INCLUDED
LED INFO:	
LUMENS:	200
COLOR TEMP:	2700k
CRI:	90
INCANDESCENT EQUIVALENCY:	1 x 20W
DIMMABLE:	Yes, on MLV dimmer only.
NOTES:	PATENT: US PATENT D736 987 S
EXTENSION:	0.5"
CERTIFICATION:	C-US WET RATED
VOLTAGE:	12V
UPC:	640665155006

AT HINKLEY, WE EMBRACE THE DESIGN PHILOSOPHY THAT YOU CAN MERGE TOGETHER THE LIGHTING, FURNITURE, ART, COLORS AND ACCESSORIES YOU LOVE INTO A BEAUTIFUL ENVIRONMENT THAT DEFINES YOUR OWN PERSONAL STYLE. WE HOPE YOU WILL BE INSPIRED BY OUR COMMITMENT TO KEEP YOUR 'LIFE AGLOW.'

*life*AGLOW®