



EnduraLED A-Shape

12A19/END/2700-800 DIM 6/1

Philips EnduraLED A-shape Dimmable LED lamps are the smart LED alternative to standard incandescents. The unique lamp design provides omi-directional light with excellent dimming performance.

Product data

• General Characteristics

Cap-Base	E26
Bulb	A19
Bulb Finish	- [-]
Rated Avg. Life (Hours)	25000 hr

• Light Technical Characteristics

Color Code	WW
Color Designation	Warm White
Beam Angle	0 D
Correlated Color Temperature	2700 K
Approximate Lumens	825 Lm
CRI	80
Color Temp. (Kelvin)	2700 K [CCT 2700K]
Rated Luminous Flux	800 Lm

• Electrical Characteristics

Wattage	12 W
---------	------

Wattage Technical	12.5 W
Voltage	120 V
Dimmable	Yes

• Product Dimensions

Overall Length C [inch]	4.255 (max) in
-------------------------	----------------


• Product Data

Product number	409946
Full product name	12A19/END/2700-800 DIM 6/1
Short product name	12A19/END/2700-800 DIM 6/1
Pieces per Sku	1
eop_pck_cfg	6
Skus/Case	6
Bar code on pack	46677409944
Bar code on case	50046677409949
Logistics code(s)	929000182902
eop_net_weight_pp	0.182 kg

PHILIPS

sense and simplicity

Dimensional drawing



E26

12W/12.5W/17W, E26, A19

Product	C (Norm)	C1 (Max)	D (Norm)	D1 (Norm)
LED 12W E26 WW 2700K 120V A19 Dimm -	4.255	-	-	2.285

For product and purchase inquiries contact:

ecoDIRECT

CLEAN ENERGY SOLUTIONS

www.ecodirect.com



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, February 1
data subject to change