



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Quicklag Industrial Thermal-Magnetic Circuit Breaker

**HBAX1020**

**UPC:**786679152645

### Dimensions:

- **Height:** 4.8 IN
- **Length:** 3.7 IN
- **Width:** 1.2 IN

**Weight:**.4 LB

**Notes:**Switching duty rated for 120V fluorescent light applications, HACR rated

### Warranties:

- 1 year

### Specifications:

- **Type:** Quicklag
- **Amperage Rating:** 20A
- **Interrupt Rating:** 42 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120/240V
- **Circuit Breaker Type:** HBAX
- **Mounting:** Bolt-on
- **Trip Type:** Non-Interchangeable
- **Quantity:** 24

### Supporting documents:

- [Eaton's Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - HBAX1020](#)

### Certifications:

- UL Listed
- CSA Certified

**Product compliance:** No Data

