



GFWT2-HGW

Brand Features

Peace of mind, all the time. The SmartlockPro Self-Test GFCI tests itself even if you forget. Designed to meet the latest UL standard for auto-monitoring (self-test) our complete line of self-test GFCIs periodically conduct an automatic internal test to confirm that it can respond to a ground fault. With the slimmest profile on the market, the device allows for fast and easy installation, while Leviton's patented reset lockout mechanism prevents reset of the GFCI if it is not wired or operating correctly. The SmartlockPro Self-Test GFCI is the smart choice in ground fault circuit interrupter protection.

Item Description

SmartlockPro GFCI Duplex Receptacle Outlet, Extra Heavy-Duty Hospital Grade, Wallplate Included, Weather and Tamper-Resistant, Power Indication, 20 Amp, 125 Volt, Back or Side Wire, NEMA 5-20R, 2-Pole, 3-Wire, Self-Grounding - White

Color: White

UPC Code: 07847772630

Country Of Origin: China

NEMA:
5-20R



Technical Information

AC Horsepower Ratings

At Rated Voltage: 1 HP

Electrical Specifications

Grounding: Self-Grounding

Pole: 2

Short Circuit Current Rating: 10kA

Wire: 3-Wire

Amperage: 20 A

Voltage: 125 VAC

Environmental Specifications

Flammability: Rated V-0 per UL 94

Operating Temperature: -35C to +66C

Material Specifications

Body Material: Polycarbonate

Face Material: PBT

Ground Clips: Brass

Grounding Screw: Stainless Steel

Line Contacts: Brass

Shutter Mechanism: Delrin® Acetal

Strap Material: Nickel Plated Steel

Terminal Clamp: Brass

Terminal Screws: Stainless Steel

Mechanical Specifications

Product ID: Ratings are permanently marked on device

Terminal Accom.: 14-10 AWG solid or stranded

Terminal ID: Black-Hot, White-Neutral, Green-Ground

Termination: Back or Side Wire

Product Features

Color: White

Grade: Extra Heavy-Duty Hospital Grade

NEMA: 5-20R

Brand: SmartlockPro

Function: GFCI

Device Type: Duplex Receptacle Outlet

Feature 2: Weather and Tamper-Resistant

Feature 3: Power Indication

Standards and Certifications

ANSI: C-73

Applicable Standards: UL 943, UL 498, CSA C22.2 No. 42 & 144, FedSpec W-C-596

Certification/Listing: UL, CSA, NOM-ANCE

NEMA: WD-1 & WD-6

Warranty

Product Warranty: 2-Year Limited

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2018 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/

