



Photocontrols : Fixed Mount Electronic Photocontrols
EK4136S | Stem Mount Electronic Photocontrol, 120-277V



8-YEAR EXTENDED WARRANTY

EK4136S

STEM MOUNT ELECTRONIC PHOTOCONTROL, 120-277V

These electronic photocontrols permanently install on outdoor electrical boxes, in-wall boxes, or outdoor lighting fixtures. Ideal for LED and new induction fixtures with long-life expectations



Features & Applications

Features

- Non-drift silicon light sensor with IR filter
- DC relay with zero-crossing circuitry for extended life
- Conformal coated PCB
- 15-year design life
- Exceeds 10,000 ON/OFF switching cycles
- Fail ON mode
- Ideal for single or multifixture HID and LED installations (up to 1,650 W @ 277 VAC)
- 255 J MOV surge protection element
- ½"-14 NPSM threaded stem fits standard outlet boxes and wall packs
- #18 AWG wire leads

Applications

- Exterior Lighting
- Street Lighting
- Parking Lot
- Pedestrian Pathway
- Landscape Lighting

Specifications

Photocontrol Style Stem Mount	Sensor Time Delay 2 sec to 5 sec	Operating Temperature Min (F) -40
Photocontrol Sensor Location Side	Surge Protection 255 J MOV	Cover Color Gray
Input Voltages Display 120-277 VAC, 50/60 Hz	Wiring Option Wire Leads	Product Height (mm) 57.2
Inductive 1800 VA, 120-277 VAC, 50/60 Hz	Wire Lead Length (in) 9	Product Width (mm) 33.3
Incandescent Load Ratings 1000 W, 120-277 VAC, 50/60 Hz	Wire Lead Length (mm) 0	Product Depth (mm) 31.8
Electronic Ballast 6 A, 120-277 VAC, 50/60 Hz	Operating Temperature Max (°C) 70	Warranty 8-year limited
Activation Off 2.25 fc	Operating Temperature Max (F) 158	Housing Material Polycarbonate
Activation On 1.5 fc	Operating Temperature Min (°C) -40	


Videos

Related Accessories and Parts (2)



6LV1352

LIGHT SHIELD FOR BUTTON PHOTOCONTROL (K4000 SERIES, K4321, K4400 SERIES, EK4036S, EK4336S, EK4436SM)



K43-WP-KIT

WALL PLATE KIT (FOR BUTTON – K4000 SERIES, EK4036S)

Copyright © 2016 Intermatic Incorporated. All rights reserved.