



A-Shape LED

14A19/LED/850 ND 120V

Philips A-shape Dimmable LED lamps are the smart LED alternative to standard incandescents. The unique lamp design provides omi-directional light with excellent dimming performance.


Product data

General Information		Starting Time (Nom)	
Cap-Base	E26 [Single Contact Medium Screw]		0.5 s
Bulb Shape	A19 (A19)	Warm Up Time To 60% Light (Nom)	0.5 s
Nominal Lifetime (Nom)	10950 h	Power Factor (Nom)	0.8
Switching Cycle	50000X	Voltage (Nom)	120 V
Technical Type	14-100W		
Light Technical		Temperature	
Color Code	850 [CCT of 5000K (2)]	T-Case Maximum (Nom)	90 °C
Initial lumen (Nom)	1500 lm		
Luminous Flux (Rated) (Nom)	1500 lm	Controls and Dimming	
Color Designation	Daylight	Dimmable	No
Correlated Color Temperature (Nom)	5000 K		
Luminous Efficacy (rated) (Nom)	107.1 lm/W	Mechanical and Housing	
Color Consistency	ANSI	Bulb Finish	Frosted (FR)
Color Rendering Index (Nom)	80		
LLMF At End Of Nominal Lifetime (Nom)	70 %	Approval and Application	
		Suitable For Accent Lighting	Yes
		Energy Consumption kWh/1000 h	14 kWh
Operating and Electrical		Product Data	
Input Frequency	60 Hz	Order product name	A19 14W 5000K E26
Power (Rated) (Nom)	14 W	EAN/UPC - Product	046677455712
Lamp Current (Nom)	228 mA	Order code	455717
Wattage Equivalent	100 W	Numerator - Quantity Per Pack	1

A-Shape LED

Numerator - Packs per outer box	4
Material Nr. (12NC)	929001135103
Net Weight (Piece)	0.052 kg

Dimensional drawing



Bulb A19 120V 14W-100W 150D 5000K E26 ND

Product	D	C
A19 14W 5000K E26	61.0 mm	107.4 mm

