



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Type GHQ Thermal-Magnetic Circuit Breakers

GHQ1020S

UPC:786685403427

### Dimensions:

- **Height:** 4 IN
- **Length:** 2.63 IN
- **Width:** 3 IN

**Notes:**Includes 4A33462H01 load clip.

### Warranties:

- 1 year

### Specifications:

- **Special Features:** 120/208/240V shunt trip
- **Amperage Rating:** 20A
- **Interrupt Rating:** 14 kAIC
- **Voltage Rating:** 277V
- **Circuit Breaker Type:** GHP
- **Trip Type:** Non-Interchangeable
- **Frame Size:** GDB-Frame

### Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - GHQ1020S](#)

**Certifications:** No Data

**Product compliance:** No Data

