



Representative Image

Catalog No. TED134040

Description: 3 POLE 480VAC 40A BREAKER

UPC No 783164063851

Products > Circuit Breakers > Molded Case Circuit Breakers > Thermal Magnetic

Thermal-Magnetic Trip. E150 Line Circuit Breakers. Noninterchangeable Trip. Includes Cu/Al load lugs only. If line lugs are required, add suffix "WL" to Product Number. UL listed for HID (high intensity discharge). All TEB, TED, THED breakers UL listed as HACR type except 10 ampere. All TEB, TED, THED breakers suitable for reverse feed. 60/75°C rating through 100 amperes, 75°C rating above 100 amperes.

Descriptors

| | |
|-------------|------------------|
| Category | Thermal Magnetic |
| GO Schedule | EB |

Specifications

| | |
|----------------|------|
| Amperage | 40 A |
| GSA Compliance | No |