

Product Specifications

Project _____

Location _____

Type _____

10563

Manufactured by Kichler® Lighting



DESCRIPTION

Task Work Module 12V Xenon -

Premium quality Xenon lamp undercabinet lighting. Modular design for easy installation and excellent light placement.

SPECIFICATIONS

MATERIALS:

Housing: Extruded Aluminum

End Caps: Polycarbonate

Lens: Frosted Glass

FINISHES: Anodized Brushed Nickel, Anodized Brushed Bronze or Powder Coated White

DIMENSIONS:

Length: 22.00"

Width: 5.00"

Height: 1.00"

LIGHT SOURCE:

- 3 – 18W Xenon lamp
- 2700K color temperature
- 100 Color Rendering Index (CRI)
- 10,000 hour expected life span

ELECTRICAL DATA:

Input Voltage: 12V AC

Power Consumed: 54 watts

Efficacy: 6 lumens/watt

FEATURES

- C-UL Listed for Cabinet Use – UL Standard No. 2108
- Unique front-mount design as recommended by the American Lighting Association
- Ability to snap fixtures together to create an even flow of light
- Captive screws for ease of installation
- Intended for connection to power from wire module
- High/Low, On/Off switch
- Plug-in master switch and wire module available and sold separate
- 9", 14" and 21" interconnect cables available in WH/BK and sold separate
- Bulb(s) included
- Built-in electronic transformer
- Hinged tempered glass diffuser
- Also available as:
 - Starter Kit (fixture, wire module and 14" interconnect cable)
 - 36" Cord and Plug version

PHOTOMETRIC DATA

Countertop Foot-Candle Measurements Available Upon Request.

FOOT-CANDLE MEASUREMENT ON WORK SURFACE

A	LIGHT OUTPUT FC (COUNTER FRONT)	28.3
B	LIGHT OUTPUT FC (COUNTER MIDDLE)	58.2
C	LIGHT OUTPUT FC (COUNTER BACK)	74.1
D	LIGHT OUTPUT FC (COUNTER WALL)	36.2

