



## 8457-12: One Light Outdoor Wall Lantern



**Collection:** Jamestowne

Large Outdoor Wall Lantern Finished in Black with Clear Beveled Glass.

Outdoor wall lantern finished in black over solid brass with clear beveled glass.

**UPC #:**785652845710

**Finish:** Black (12)

### Dimensions:

**Width:** 5 1/4"

**Height:** 12 1/2"

**Weight:** 2.7 lbs.

**Extends:** 5 3/4"

**Wire:** 6 1/2"

**Mounting Proc.:** Cap Nuts

**Connection:** Mounted To Box

**Bulb Appearance:** Clear

### Bulbs:

1 - Medium A19 100w Max. 120v - Not included

### Features:

- Clear bulb(s) recommended for this fixture
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

### Material List:

- 1 Body - Aluminum - Black
- 1 Canopy - Aluminum - Black
- 1 Bracket - Aluminum - Black
- 1 Candle Cup - Aluminum - Black

### Safety Listing:

Safety Listed for Wet Locations  
Safety Listed for Wet Locations

### Instruction Sheets:

English (HC-231)  
French (F-009)

### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Glass	Clear Beveled	4			3 7/16	5 1/2					

### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate			2 1/8	4 1/2	6	6 1/2

### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	8457-12	1	785652845710	7.5	6.5	11.5	0.324	3.4	93	Yes
Master Pack		3	10785652845717	20.25	8	12.5	1.172	11.35	93	Yes
NJ Pallet		204		48	40	72	80	772		No
NV Pallet		204		48	40	72	80	772		No