



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## BR style 1-inch commercial loadcenter

**3BR3042B200**

**UPC:** 786676440707

**Dimensions:** 3.88 IN \* 14.31 IN \* 29.13 IN (L \* W \* H)

**Notes:** Listed for use as service entrance equipment and shipped with a neutral bonding strap preattached, the maximum rating of the panel is the main breaker rating when used as service entrance equipment.

**Warranty:** 10 year

### Specifications:

- **Special Features:** No feed-thru lugs
- **Type:** Main circuit breaker
- **Amperage Rating:** 200A
- **Box Size:** L1
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** BWH
- **Number Of Circuits:** 42
- **Number Of Spaces:** 30
- **Number Of Wires:** Four-wire
- **Phase:** Three-phase
- **Wire Size:** #1-250 kcmil Cu/Al at 60°C or 75°C
- **Mounting:** Combination
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 208Y/120 or 240V

### Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Type BR 3-Phase Loadcenters](#)



- [3-Phase Loadcenter Program](#)

**Certifications:** No Data

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.