



Measurements:

<u>Height</u>	<u>Width</u>	<u>Length</u>	
13.00"	34.00"	34.00"	
<u>Max OAH</u>	<u>Min OAH</u>		
137.00"	17.00"		
<u>Hanging Weight</u>	<u>Canopy Width</u>	<u>Canopy Height</u>	<u>Canopy Length</u>
17.20 lb	8.75"	1.50"	8.75"

Lamping:

LED PCB LED	5,897 Rated Lumens
9 9.36W PCB LED	3000 Color Temperature
84.24 total watt	80 CRI
Dimmable : Standard Triac/Lutron® or Leviton® CL	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
25.40 lb	34.30"	12.20"	34.30"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	845094077121	Yes	

Finish:

Polished Chrome PC

Material:

Aluminum + Acrylic + Steel

Certification:

Dry Location

Additional:

PCB LED (Included)
Adjustable