



# Candle LED

## 10G25/LED/827-22/E26/CL/DIM 120V

Philips Candle Dimmable LED Lamps offer decorative energy saving ambience with the elegant effect of incandescent candles. Available in bent, blunt and flame tip candles, their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.

### Product data


| General Information                   |                                    | Starting Time (Nom)             |                                  |
|---------------------------------------|------------------------------------|---------------------------------|----------------------------------|
| Cap-Base                              | E26 [ Single Contact Medium Screw] |                                 | 0.5 s                            |
| Bulb Shape                            | G25 (G25)                          | Warm Up Time To 60% Light (Nom) | instant full light               |
| Nominal Lifetime (Nom)                | 25000 h                            | Power Factor (Nom)              | 0.9                              |
| Switching Cycle                       | 50000X                             | Voltage (Nom)                   | 120 V                            |
| Technical Type                        | 10-60 W                            |                                 |                                  |
| Light Technical                       |                                    | Temperature                     |                                  |
| Color Code                            | 822-827 [ tunable warm white]      | T-Case Maximum (Nom)            | 90 °C                            |
| Luminous Flux (Nom)                   | 800 lm                             |                                 |                                  |
| Luminous Flux (Rated) (Nom)           | 800 lm                             | Controls and Dimming            |                                  |
| Color Designation                     | Warm White (WW)                    | Dimmable                        | Yes                              |
| Correlated Color Temperature (Nom)    | 2200-2700 K                        |                                 |                                  |
| Color Consistency                     | ANSI 2700K                         | Mechanical and Housing          |                                  |
| Color Rendering Index (Nom)           | 80                                 | Bulb Finish                     | Clear                            |
| LLMF At End Of Nominal Lifetime (Nom) | 70 %                               |                                 |                                  |
| Operating and Electrical              |                                    | Approval and Application        |                                  |
| Input Frequency                       | 60 Hz                              | Suitable For Accent Lighting    | No                               |
| Power (Rated) (Nom)                   | 10 W                               | Energy Efficiency Label (EEL)   | Not applicable                   |
| Lamp Current (Nom)                    | 97 mA                              | Energy Consumption kWh/1000 h   | 10 kWh                           |
| Wattage Equivalent                    | 60 W                               |                                 |                                  |
|                                       |                                    | Product Data                    |                                  |
|                                       |                                    | Order product name              | 10G25/LED/827-22/E26/CL/DIM 120V |
|                                       |                                    | EAN/UPC - Product               | 046677459345                     |

## Candle LED

|                                 |              |
|---------------------------------|--------------|
| Order code                      | 929001189804 |
| Numerator - Quantity Per Pack   | 1            |
| Numerator - Packs per outer box | 6            |
| Material Nr. (12NC)             | 929001189804 |

|                    |          |
|--------------------|----------|
| Net Weight (Piece) | 0.105 kg |
|--------------------|----------|

### Dimensional drawing



LED 10-60W E26 G25 CL DIM

| Product                          | D     | C      |
|----------------------------------|-------|--------|
| 10G25/LED/827-22/E26/CL/DIM 120V | 78 mm | 122 mm |

