


ARGOS – model: LED25

LEDme® Track / Rail Luminaire

WAC LIGHTING

Responsible Lighting®



Fixture Type:

Catalog Number:

Project:

Location:

PRODUCT DESCRIPTION

A celebration of the SSL revolution, designed exclusively around LED technology, breaking through the conventions of earlier light sources. The rectangular form is derived from the optimal format for LED design on a PCB for thermal to surface area ratios. Engineered with minimal components, perfect balance precision aiming, and a single diffuser that can be easily removed with a tool-free mechanism. Developed for the most challenging applications in upscale residential and commercial environments.

FEATURES

- Energy Star® rated
- Free of projected heat and UV and IR radiation
- Single tool-free lens assembly for easy in field change out of beam angle
- Available in two interchangeable optics that may be ordered separately
- Replaceable LED modules
- 360° horizontal and 90° vertical "hot" aiming
- 100,000 hour rated life
- 5 year WAC Lighting product warranty

FIXTURE PERFORMANCE

Model #	Beam	Color Temp	Watt	Lumens	Efficacy	CBCP	CRI
LED25S-27	20°	2700K	25	1360	54 Lm/W	4923	85
LED25F-27	42°			1210	48 Lm/W	1831	
LED25S-30	20°	3000K	25	1480	59 Lm/W	5868	85
LED25F-30	42°			1320	53 Lm/W	1948	
LED25S-35	20°	3500K	25	1505	60 Lm/W	5087	85
LED25F-35	42°			1330	53 Lm/W	1860	
LED25S-40	20°	4000K	25	1525	61 Lm/W	5472	80
LED25F-40	42°			1345	54 Lm/W	2017	

SPECIFICATIONS

Construction: Die-cast aluminum with front lens assembly.

Finish: Black (BK), Dark Bronze (DB), Platinum (PT - W Track and Flexrail only), and White (WT) powder coat paint.

Driver: Input voltage: 120VAC or 277VAC 50/60Hz, Max. Load: 25W

Light Source: 10 pieces Cree XT-E LED.

Dimming: LED lamp dims to 10% with electronic low voltage (ELV) dimmer.

Standards: ETL & cETL Listed.

System	Model	Beam	Color Temp	Finish
L L Track 120V	LED25	S 20°	27 2700K	BK Black
H H Track 120V				WT White
J J/J2 Track 120V				BK Black
WTK W Track 120V				PT Platinum
WHK W Track 277V				WT White
HM1 Flexrail™ 120V				DB Dark Bronze PT Platinum

FINISHES



REPLACEABLE LED MODULES

Model	Color Temp
RM-10X3-27	2700K
RM-10X3-30	3000K
RM-10X3-35	3500K
RM-10X3-40	4000K

INTERCHANGABLE OPTICS

Model	Beam
OPH-10X3-20D	20°
OPH-10X3-42D	42°

- **LED25** - - -

Example: L-LED25S-40 -BK

WAC Lighting
www.waclighting.com
Phone (800) 526.2588 • Fax (800) 526.2585

Headquarters/Eastern Distribution Center
44 Harbor Park Drive • Port Washington, NY 11050
Phone (516) 515.5000 • Fax (516) 515.5050

Western Distribution Center
1750 Archibald Avenue • Ontario, CA 91760
Phone (800) 526.2588 • Fax (800) 526.2585

ARGOS – model: LED25

Photometrics

WAC LIGHTING

Responsible Lighting®

FIXTURE PERFORMANCE – 3000K

 0° Aiming Angle (ceiling to floor)

LED25S-30 20° beam

Distance	FC	L	W
6 ft	162	1.9	1.9
9 ft	72	2.8	2.8
12 ft	40	3.8	3.8
15 ft	26	4.7	4.7

LED25F-30 42° beam

Distance	FC	L	W
6 ft	54	4.5	4.5
9 ft	24	6.8	6.8
12 ft	14	9.1	9.1
15 ft	9	11.3	11.3



 45° Aiming Angle (ceiling to wall)

LED25S-30 20° beam

Distance	FC	L	W
6 ft	57	3.9	2.7
9 ft	25	5.8	4.0
12 ft	14	7.7	5.3
15 ft	9	9.6	6.6

LED25F-30 42° beam

Distance	FC	L	W
6 ft	19	10.6	6.4
9 ft	8	15.9	9.6
12 ft	5	21.2	12.8
15 ft	3	26.4	16.0



FC– Initial footcandle level at the center of the beam
L– Beam length at the point the candlepower drops off to 50% of maximum*
W– Beam width at the point the candlepower drops off to 50% of maximum*
 *Measured in feet

WAC Lighting
 www.waclighting.com
 Phone (800) 526.2588 • Fax (800) 526.2585

Headquarters/Eastern Distribution Center
 44 Harbor Park Drive • Port Washington, NY 11050
 Phone (516) 515.5000 • Fax (516) 515.5050

Western Distribution Center
 1750 Archibald Avenue • Ontario, CA 91760
 Phone (800) 526.2588 • Fax (800) 526.2585