

30A 3P 600V 3W NON-FUSED HD TYPE 4X



General technical data

Manner of function of the actuating element	SINGLE THROW
Mechanical service life (switching cycles) typical	10000
Mounting type	2 OR 3 POINT MOUNTING HOLES
Number of poles	3

Electricity

Ampacity	30 A
Supply voltage frequency rated value 50/60 Hz	Yes
Voltage between phase and Ground (GND) rated value	600 V

Switching capacity

Switching capacity active power	3 W
---------------------------------	-----

Model

product brandname	SIEMENS
Product type designation	ENCLOSED/SAFETY SWITCH

Mechanical Design

Design of the housing	TYPE 4X
Material	SS

General product approval

Certificate of suitability

UL

last modified:

02/22/2017