



Hoffman

ULTRX, Type 4X

Catalog Number: UU606030W
US List Price (USD): \$1,057.00

Bulletin Number:

- UX1

Material:

- Fiberglass



Model Code:

- 35870

Ship Wt. Std. Pkg. (lbs):

- 36.58

Interchangeable:

- False

Industry Standards:

Mounting brackets required to meet UL/CSA external mounting requirements. UL 508A Listed; Type 3, 3R, 4, 4X, 12, 13; File No. E61997 cUL Listed per CSA C22.2 No 94; Type 3, 3R, 4, 4X, 12, 13; File No. E619977 Enclosure flammability evaluated per UL 508A Window flammability evaluated per UL 508A NEMA/EEMAC Type 3, 3R, 4, 4X, 12, 13 CSA File No. 42186: Type 3, 3R, 4, 4X, 12, 13 IEC 60529, IP66 Meets NEMA Type 3RX requirements

Description

Providing outstanding protection against corrosion and the elements, the clean lines and molded, embossed design of ULTRX™ fiberglass enclosures make them the most stylish and aesthetically pleasing of their class. These enclosures feature hidden hinges, a padlocking capability for security, and flexible internal mounting options.

Applications:

Providing outstanding protection against corrosion and the elements, the clean lines and molded, embossed design of ULTRX™ fiberglass enclosures make them the most stylish and aesthetically pleasing of their class.

Specifications:

- Compression-molded fiberglass material has excellent temperature and chemical resistance qualities and exhibits outstanding physical properties, including high-impact resistance
- Fiberglass is easily punched, drilled, filed or sawed
- Seamless foam-in-place gasket assures water-tight and dust-tight seal
- Enclosure may be rotated 180 degrees for left and right hinging
- Molded-in drip shields are standard with each enclosure
- Impact-resistant polycarbonate window is permanently bonded in place
- Fiberglass mounting brackets and stainless steel attachment screws are provided with each enclosure
- Unique hinge design allows for standard 180 degree door opening with a maximum opening of 270 degrees
- Door hinges are replaceable
- Type 316 stainless steel quarter-turn latch. Optional keylocking or padlocking handle available.
- Molded-in DIN bosses
- Molded bosses on door provide additional mounting provisions
- Integral mounting rails provide infinite panel adjustment front to back
- Optional data pocket is high-impact thermoplastic

Finish:

Exterior surface painted light-gray acrylic enamel for enhanced UV protection. Optional steel panels are painted white. Optional stainless steel, aluminum, conductive and composite panels are unpainted.

Accessories:

- H2OMIT™ Vent Drains, Type 4X
- H2OMIT™ Thermoelectric Dehumidifier
- HOL-SEALERS™ Non-Metallic Hole Seals
- Panels for Type 3R, 4, 4X, 12 and 13 Enclosures
- Rack Angles (Type RA)

Modifications and Customizations:

Hoffman excels at modifying and customizing products to your specifications. Contact your local Hoffman sales office or distributor for complete information

Notes:

- Purchase panels separately.
- When installing enclosures in a right-hand hinge application that involves vibration, Hoffman recommends the use of pad-locking or key-locking quarter-turn latch accessories for door securement (UUHPL, UUHKL).

Technical Data

ULTRX, Type 4X

Catalog Number	UU606030W
A in.	23.62
B in.	23.62
C in.	11.81
K in.	0.83
F in.	11.30
Panel Size D x E in.	20.98 x 20.98
S in.	19.25
Window Size M x N in.	19.61 x 19.13
J in.	19.68
Conductive Panel	A24P24G
Mounting G x H in.	21.85 x 22.36
External Dimensions L x W in.	24.61 x 24.09
Panel	A24P24
Internal Dimensions A x B x C in.	23.94 x 23.43 x 12.64


Certifications


 EU Certification

 UL Certification

Documents

 Spec Sheet

 Instruction Manual

 Instruction Manual

 3D STEP CAD




 2D DXF CAD

 66131fg

 Instruction Manual

 Dimension Drawing

Accessories

Item		
	PANELITE LED Enclosure Light	LED24V15
	HOL-SEALERS Non-Metallic Hole Seals	ASPB05075NM
	24V w/ SS shroud	TE121024011