



5328-962: Two Light Ceiling Flush Mount



Collection: Webster

Two Light Wall or Ceiling Fixture in Brushed Nickel Finish with White Bowl-Shaped Glass.

Two-light close to ceiling fixture with brushed nickel finish and white glass.

UPC #:785652532894

Finish: Brushed Nickel (962)

Dimensions:

Diameter: 9 1/2"

Height: 5 3/4"

Extends: 5 3/4"

Wire: 6 1/2"

Mounting Proc.: Center Lock-Up

Connection: Mounted To Box

Bulbs:

2 - Medium A19 60w Max. 120v - Not included
2 - LED Medium A19 8w Max. 120v - Not included
2 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Fixture may be mounted on wall or ceiling.
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

1 Body - Steel - Brushed Nickel

Safety Listing:

Safety Listed for Damp Locations
Safety Listed for Damp Locations

Instruction Sheets:

English (HC-167)
French (F-014)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Diffuser	Glass	Smooth White	1				4	9 1/2				

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	5328-962	1	785652532894	10.25	10.5	6.58	0.41	2.8	125	Yes
Master Pack		6	10785652532891	20.25	11	21.75	2.804	17.8	125	Yes
NJ Pallet		144		48	40	70	77.778	427.2		No
NV Pallet		144		48	40	68.25	75.833	427.2		No