



## HORIZONTAL DECK LIGHT 1546BZ-LED

BRONZE

WIDTH:	4.8"
HEIGHT:	3.0"
WEIGHT:	1.0 LBS
MATERIAL:	DIE CAST ALUMINUM
SOCKET:	1-1.50W LED *INCLUDED
<b>LED INFO:</b>	
LUMENS:	120
COLOR TEMP:	2700k
CRI:	80
LED WATTAGE:	2w
INCANDESCENT EQUIVALENCY:	12w
DIMMABLE:	Yes, on MLV dimmer only.
NOTES:	1.5W LED 2.4VA. A WIRING KIT IS SUPPLIED.
LEADWIRE:	16.0"
CERTIFICATION:	C-US WET RATED
VOLTAGE:	12V
UPC:	640665154658

AT HINKLEY, WE EMBRACE THE DESIGN PHILOSOPHY THAT YOU CAN MERGE TOGETHER THE LIGHTING, FURNITURE, ART, COLORS AND ACCESSORIES YOU LOVE INTO A BEAUTIFUL ENVIRONMENT THAT DEFINES YOUR OWN PERSONAL STYLE. WE HOPE YOU WILL BE INSPIRED BY OUR COMMITMENT TO KEEP YOUR 'LIFE AGLOW.'

*life*AGLOW®