



S9341

18.5W/LED/9"FLUSH/27K/SQ/BN
 18.5 watt; 9" Flush Mount LED Fixture; 2700K; Square Shape;
 Brushed Nickel Finish; 120 volts



Features

- Surface mount fixture
- Solid State LED lighting
- Long life
- 5 Year limited warranty
- Dimmable
- Damp location rated

S9341

Item Number	Product Line	UPC	Voltage	Watts	Incandescent Equivalent	Fixture Type	Base
S9341	BLINK	045923093418	120	18.5	100W	Flush Mount	Connector

Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
18.5W/LED/9"FLUSH/27K/SQ/BN	Dimmable	Compatible dimmers for S9341	Brushed Nickel	1"	9.00"	1100	40000

Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR
2700	Warm White	80+	108	-18C (0F) to a maximum of +46C (+115F)	12	Box	ENERGY STAR

Material	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty
Housing: Die cast aluminum	Yes	Yes	cETLus - Damp Location Rated	5 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

