



Fixture Type:

Catalog Number:

Project: _____

Location: _____

PRODUCT DESCRIPTION

Multiple mid-powered LEDs illuminate the acrylic diffuser uniformly without socket shadows which are common in conventional flush mounts.

FEATURES

- Energy Star® rated
- Damp location listed
- CSA listed
- ADA compliant for FM-211 and FM-214
- Wall or Ceiling Mount
- Opaque acrylic diffuser
- Multiple LED array for uniform illumination
- 120VAC - no driver needed
- Smooth and continuous ELV dimming
- 85 CRI
- 100% - 10% dimming
- 50,000 hour rated life
- 5 year warranty

SPECIFICATIONS

Construction: Aluminum with white acrylic diffuser

Input: 120VAC

Harmonic Distortion (THD): 20%

Operating Temperature: -35°C (-31°F) to 50°C (122°F)

ORDERING NUMBER

	Watt	Color Temp	LED Lumens	Delivered Lumens	Finish
<p>FM-211 15W</p>	<p>27 2700K 1195</p> <p>35 3500K 1215</p>	<p>985</p> <p>1035</p>	WT White		
<p>FM-214 24W</p>	<p>27 2700K 1695</p> <p>35 3500K 1775</p>	<p>1395</p> <p>1510</p>			
<p>FM-216 33.5W</p>	<p>27 2700K 2475</p> <p>35 3500K 2595</p>	<p>2060</p> <p>2150</p>			

FM - - - WT

Example: **FM-214-35-WT**

waclighting.com
Phone (800) 526.2588
Fax (800) 526.2585

Headquarters/Eastern Distribution Center
44 Harbor Park Drive
Port Washington, NY 11050

Central Distribution Center
1600 Distribution Ct
Lithia Springs, GA 30122

Western Distribution Center
1750 Archibald Avenue
Ontario, CA 91760