

6011ADW-25



## ***Steel City***

Adjustable bar hanger for 3/8 in., 1/2 in. and 5/8 in. wall board and plaster. Score marks for drywall and plaster depths. Maximum load capacity: 50 lb. (22.7). Packaged complete with fastener.

### General

Type:	Bar Hangers and Brackets
T&B UPC:	78599115485
T&B Status:	M
Material:	Steel

### Dimension Information

Depth (in.):	1-3/16
Length (in.):	14-1/2 to 26-1/2