



# Candle/Decorative LED

## 2.7B12/LED/827-22/E12/DIM 120V

Philips Candle Dimmable LED Lamps offer decorative energy saving ambience with the elegant effect of incandescent candles. Available in bent, blunt and flame tip candles, their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.

### Product data


General Information		Wattage Equivalent	
Cap-Base	E12 [ Candelabra Screw]		25 W
Bulb Shape	B12	Starting Time (Nom)	0.5 s
Nominal Lifetime (Nom)	25000 h	Warm Up Time To 60% Light (Nom)	0.5 s
Switching Cycle	50000X	Power Factor (Nom)	0.7
Technical Type	2.7-25W	Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	822-827 [ tunable warm white]	T-Case Maximum (Nom)	90 °C
Initial lumen (Nom)	180 lm	Controls and Dimming	
Luminous Flux (Rated) (Nom)	180 lm	Dimmable	Yes
Color Designation	Warm Glow(WG)	Mechanical and Housing	
Correlated Color Temperature (Nom)	2200-2700 K	Bulb Finish	Clear (CL)
Luminous Efficacy (rated) (Nom)	66.67 lm/W	Approval and Application	
Color Consistency	<6	Suitable For Accent Lighting	No
Color Rendering Index (Nom)	80	Energy Efficiency Label (EEL)	Not applicable
LLMF At End Of Nominal Lifetime (Nom)	70 %	Product Data	
Operating and Electrical		Order product name	2.7B12/LED/827-22/E12/DIM 120V
Input Frequency	60 Hz	EAN/UPC - Product	046677457235
Power (Rated) (Nom)	2.7 W		
Lamp Current (Nom)	35 mA		

## Candle/Decorative LED

Order code	457234
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001166804

Net Weight (Piece)	0.048 kg
--------------------	----------

### Dimensional drawing



LED 3.5-25W E12 B12 CL DIM

Product	D	C
2.7B12/LED/827-22/E12/DIM 120V	38 mm	110 mm

Photometric data

General Uniform Lighting

