



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Quicklag Industrial Thermal-Magnetic Circuit Breaker

**BAB2035**

**UPC:** 786679302354

**Dimensions:** 3.8 IN \* 2.3 IN \* 4.8 IN (L \* W \* H)

**Notes:** HACR rated

**Warranty:** 1 year

### Specifications:

- **Type:** Quicklag
- **Quantity:** 12
- **Mounting:** Bolt-on
- **Circuit Breaker Type:** BAB
- **Trip Type:** Non-Interchangeable
- **Amperage Rating:** 35A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 120/240V

### Supporting documents:

- [Eatons Volume 4-Circuit Protection Catalog](#)
- [Eaton Specification Sheet - BAB2035 Specification](#)

### Certifications:

- CSA Certified
- UL Listed

**Product compliance:** No Data

