

## IEC Pin and Sleeve

60A, 3 Phase 250V, 3 Pole, 4 Wire

## Low Profile Pin and Sleeve Plug

# HUBBELL



### Features

- Solid one-piece pins for reliable electrical contact
- Integrated Cord Grip limits strain on terminals

### Ordering Information

Description	UPC	Catalog Number
Low Profile Pin and Sleeve, 60A 250V, 3P4W	783585507804	A460P9

**Device Color**  
Blue




### Specifications

Case	Zytel® 101 Nylon
Shroud	Zytel® 101 Nylon
Pins	Brass CDA #360
Pin and Carrier	High-Impact Thermoset
Terminal Screws	Stainless Steel

### Performance

<b>Electrical</b>	
Current Interrupting	Certified for current interruption at full rated current
Dielectric Voltage	Withstands 3,000V AC
Max Working Voltage	250V RMS
<b>Mechanical</b>	
Impact Resistance	Per CSA C22.2 No. 182.1 / UL1682
Product Identification	Ratings are a permanent part of the device housing
Terminal Identification	Terminals identified in accordance with North American convention
<b>Environmental</b>	
Flammability	HB or better per UL 94 or CSA C22.2 No. 0.17
Ingress Protection	IP22 Suitability
Operating Temperatures	Max. Continuous +75°C; Min. -40°C w/o impact



### Online Resources

Customer Use Drawing  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

