



Other

**Catalog Number:** IBG20-40  
**Product ID:** 7TAA014170R0003  
**UPC Number:** 78621080240  
**EAN Number:** 05415022348859  
**Status:** Active

E-Z-Ground I-Beam Steel Compression Connector for Cable Range 2/0 - 4/0 AWG

- Breakaway bolt head shears at predetermined torque to ensure tight connection. Heavy-duty compression lug provides excellent current carrying capabilities.
- Connector made of high-conductivity cast copper bright dip. Clamp made of drop-forged high-grade steel, zinc plated.
- Application Tools: TBM15I

### North American Specifications (UNSPSC)

UNSPSC	39121613 Grounding devices or assemblies
IGCC	4909 Grounding devices or assemblies
Brand Name	Blackburn
Type	E-Z-Ground Compression Grounding
Special Features	Breakaway bolt head shears at predetermined torque to ensure tight connection. Heavy-duty compression lug provides excellent current carrying capabilities.
Standard	UL E3060
Conductor Material	Steel
Insulation	No

### Packaging

Inner Quantity	2
Inner Dimensions (inches)	4.3x3.3x4.3
Outer Quantity	10
Outer Dimensions (inches)	21.5x4.4x3.5
Weight Uom	147.5 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website
Instruction Sheet 1	ta01417-tb2

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: techsupport@tnb.com