

Project Name

Location

Prepared By



Notes

General

Status	Active
Watts	13
Incandescent Equivalent	50
Volts	120V
Shape	PAR30SN
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	3500
Temperature	Neutral White
CRI	82
Lumens	1000
Beam Spread	40
Dimmable	Yes Dimmable
Hours Rated	25000
Lamp Type	PAR
Technology	LED

Electrical

CBCP	850
Dimmable Down To	10
Power Factor	1
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	3.63
MOD	3.75
Housing Color	Silver

Additional Information

Enclosure Rating	Enclosed Rated Lamp
Rated For Enclosed Fixture	Yes
IP Rating	IP65
Warranty	3 Year Limited

Compliance

Safety Listing	cULus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2289477
CEC Status	Non-Compliant
RoHS Compliant	Yes
SDS Sheet	LED_Lamp