



Item #: **F887-96-BN**
 Product Family Name: **Xtreme**
 Category: **Interior Fan**
 Certification: **3171583**
 Patents:
 Notes:

UPC Code: **706411052750**
 Finish: **Xtreme**
 Category Type: **Ceiling Fan**

Image File Name:
 F887-96-BN--
 1422613576.jpg



MEASUREMENTS

Blade Finish: Reversible Blades: **No**
 Blade Material: **ALUMINUM** Slope: **No**
 Blade Sweep: **96** No. of Blades: **9** Blade Pitch: **4 DEGREES** Hanging Weight: **24.91**
 Downrod 1: **3.5** Downrod 1 Outside Dia: **.75** Downrod 2: **6.0** Downrod 2 Outside Dia: **.75**
 Ceiling to Lowest Point: (Dim A) **11.00** Ceiling to Blade: (Dim B) **9.50** Lead Wire: **80** Motor Size: **DC 165Lx25mm**

	Low:	Low/Med:	Medium:	Med/High:	High:
RPM:	51	54.00	59	64.00	72
Amps:	0.15	0.18	0.22	0.25	0.39
Watts:	10.760	13.17	16.010	19.16	30.480
CFM:	9152.00	9249.00	10326.00	11501.00	13080.00
CFM/Watts	850.32	701.85	644.93	600.35	429.13



FAN CONTROLS

Pull Chain Control: **No**
 Works with Remote Control: **Yes**
 Included Remote Control: **RC400**
 Compatible Remote Control[s]:
 Works with Wall Control: **No**
 Included Wall Control:
 Compatible Wall Control[s]:

LAMPING

No. of Bulbs: Light Type:
 Max Bulb Wattage: Socket:
 Light Kit: Dimmable: Ballast: Rated Life Hours: Uplight
No **No**
 Lamp Included: Color Temp.: CRI: Initial Lumens: Delivered Lumens:
No

GLASS

Description: Material:
 Part No.: Quantity:
 Width: Height: Length:



SHIPPING

Carton Width: **10.500** Carton Height: **10.500** Carton Length: **45.750**
 Carton Weight: **29.700** Carton Cubit Feet: **2.919** Small Package Shippable: **Yes**
 Master Pack Width: Master Pack Height: Master Pack Length:
 Master Pack Weight: Master Cubic Feet: Multi-Pack: Master Pack: **1**



ETL Intertek

Yes