



# Energy Saver Reflectors

## BC-EL/A R20 13W 3/1

Looking for an energy saver that doesn't look like one? The Philips EnergySaver family provides energy efficient lighting options that don't just provide similar light as your standard incandescent light bulb, they also have the same classic shapes. Philips Energy Saver reflector flood compact fluorescents reduce operating costs without sacrificing light quality compared to incandescent equivalents. With dimmable and hard glass options, they are ideal for recessed and track lighting indoors and outdoors.

### Product data

General Information	
Cap-Base	E26 [ Single Contact Medium Screw]
Bulb Shape	EL/A R20
Switching Cycle	4000X

Light Technical	
Color Code	827 [ CCT of 2700K]
Luminous Flux (Rated) (Nom)	470 lm
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	463
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	36 lm/W
Color Rendering Index (Min)	80

Operating and Electrical	
Input Frequency	50 or 60 Hz
Power (Rated) (Nom)	13 W
Lamp Current (Nom)	220 mA
Wattage Equivalent	50 W

Warm Up Time To 60% Light (Max)	180 s
Power Factor (Nom)	0.55
Voltage (Nom)	110-127 V

Controls and Dimming	
Dimmable	No

Approval and Application	
Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	1.5 mg


  

Product Data	
Order product name	BC-EL/A R20 13W 3/1
EAN/UPC - Product	046677426835
Order code	929689963502
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	3
Material Nr. (12NC)	929689963502
Net Weight (Piece)	0.072 kg

## Energy Saver Reflectors

---

### Dimensional drawing



Product	D	C	F
---------	---	---	---

Reflector R20 13W/827 E26 110-127V

