



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YAZ342TC38  
 7818100654644  
 500CULUG-LONG-OPEN-3/8X1  
 Active

**Web Use**  
 BURNDY Product Line

Tongue Angle  
 Strip Length  
 Length (in)  
 Tongue Type  
 Barrell Style  
 Bolt Hole Size (in)  
 Barrel Type  
 Thickness  
 B Length (in)  
 Pad Width (in)  
 E - in

**Dimensional**

Straight  
 2-5/16  
 4.85  
 Standard  
 Skived  
 0.39  
 Long  
 0.23  
 2.25  
 1.55  
 1.00

Number of Holes  
 Product Description

**General**

2  
 Copper Compression Lug, 2 Hole  
 w/ Inspection Window, 500 Flex,  
 3/8" Stud, 1" Stud Hole Spacing,  
 Long Barrel, Tin Plated

Copper Solid Size (Range)  
 Navy Cable Size (Range)  
 Copper Stranded (Range)

**Conductor(s)**

N/A  
 N/A  
 500 kcmil

Type of Plating  
 Bolt Hole Size  
 Color Code  
 Plated (Yes or No)  
 Index Number  
 Product Material

**Physical**

Tin - Electro Plated  
 3/8  
 Brown  
 Y  
 20,299  
 Copper

UL Listed  
 CSA Certified  
 ROHS Compatible  
 UL Recognized  
 CULUS

**Approvals / Certifications**

Y  
 Y  
 Compliant  
 N  
 N

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175