



**Catalog No. CL07A311MJ**

**Description: CL07A311MJ-C CONT. 110V50**

**UPC No 842509504243**

**Products > Contactors > IEC Contactors > Contactor**

IEC Contactors. C-2000 Nonreversing and Reversing. AC Controlled, 3-Pole. HP Ratings AC-3 Duty. 5-75 Hp (460V) Nonreversing Standard Terminals. A 1NO and 1NC front-mounted auxiliary contact block are supplied (unassembled) with contactors that begin with CL06, CL07, CL08, CL09, and CL10. Add suffix "S" to product number for 1NO-1NC side auxiliary (assembled). Maximum Current @ 460 V (A) AC-3: 62A. 1-Phase HP @60 Hz, 115V: 5. 1-Phase HP @60 Hz, 230V: 10. 3-Phase HP @60 Hz, 200V: 20. 3-Phase HP @60 Hz, 230V: 20. 3-Phase HP @60 Hz, 460V: 40. 3-Phase HP @60 Hz, 575V: 50. KW @ 50 Hz, 380/415V: 30.

**Descriptors**

Category	Contactors
GO Schedule	C2

**Specifications**

Contacts	1NO-1NC
Coil Voltage	110 (50 Hz) / 120 (60 Hz)

## Publications

Title	Publication No.	Publication Type
C2000 CL06_07_08A311M		
GEP1260-05-023C2000 CL06_07_08A311M	GEP1260-05-023	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.