



Hoffman

Hinge-Cover, Medium, Type 3R

Catalog Number: A16R126HCR
US List Price (USD): \$145.00

Bulletin Number:

- A3M

Material:

- Steel



Model Code:

- 38670

Ship Wt. Std. Pkg. (lbs):

- 18.0

Interchangeable:

- False

Industry Standards:

UL 50, 50E Listed; Type 3R; File No. E27567 cUL Listed per CSA C22.2 No 94;
Type 3R File No. E27567 NEMA/EEMAC Type 3R IEC 60529, IP32

Description

These enclosures have a size range of 16 x 12 x 6-in. to 48 x 36 x 16-in. and meet basic functionality requirements for applications that require protection from rain, sleet, snow or dripping water.

Application:

These enclosures have a size range of 16 x 12 x 6-in. to 48 x 36 x 16-in. and meet basic functionality requirements for applications that require protection from rain, sleet, snow or dripping water.

Features:

- Drip shield top and seam-free sides, front, and back protect from rain, snow, or sleet
- 16 gauge plated steel continuous hinge has stainless steel pin
- Cover fastened securely with captive plated steel screws
- Collar studs provided for mounting optional panels
- Hasp and staple provided for padlocking
- No gasketing or knockouts

Specifications:

16 or 14 gauge galvanized steel

Finish:

ANSI 61 gray polyester powder paint finish inside and out over galvanized steel. Optional solid panels are white.

Accessories:

- Industrial Corrosion Inhibitors
- Electric Heater
- Grounding Device

- Panels for Type 3R, 4, 4X, 12 and 13 Enclosures
- Rack Mounting Angles - U Style (Type RA)
- Touch-Up Paint
- Steel and Stainless Steel Window Kits

Notes:

- Purchase panels separately. Optional aluminum panels are available for most sizes.
- Purchase perforated panels separately.
- Flanged on all four sides.

Technical Data

Hinge-Cover, Medium, Type 3R

Catalog Number	A16R126HCR
A in.	16
B in.	12
C in.	6
Panel Size D x E in.	13.00 x 9.00
Mounting G x H in.	17.00 x 3.00
Panel	A16P12
Perforated Panel	A16P12PP
Overall L in.	18.00

Certifications



EU Certification



UL Certification

Documents



Spec Sheet



Instruction Manual



3D STEP CAD













2D DXF CAD



Dimension Drawing

Accessories

Item			
	Panels for Type 3R, 4, 4X, 12 and 13 Enclosures	A16P12	
	Perforated Panels	A16P12PP	
	Panels for Type 3R, 4, 4X, 12 and 13 Enclosures	A16P12AL	
	Grounding Device	AGS816	
	Grounding Device	AGLK2	
	Grounding Device	AGS408	
	Grounding Device	AGS416	
	Grounding Device	AGS808	
	Steel and Stainless Steel Window Kits	APWK95NF	
	Touch-Up Paint	ATPPY61	