



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## NEMA Freedom Series Non-Reversing Reset Overload Relay Starter

**AN16BN0AC**

**UPC:** 782113971568

**Dimensions:** 4.61 IN \* 4.38 IN \* 3.31 IN (L \* W \* H)

**Notes:** Heater Packs must be purchased separately

**Warranty:** Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Special Features:** Starter w/C306 bi-metal OLR
- **Amperage Rating:** 18A
- **Max Hp Rating:** 1 hp at 115V, 2 hp at 230V, 3 hp at 208,240V, 5 hp at 480,600V
- **Mounting:** Horizontal
- **Number Of Poles:** Three-pole
- **Phase:** Single-phase, three-phase
- **Size:** 0

### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [AN16BN0\\_C AutoCAD 2D Footprint \(mm\)](#)
- [AN16BN0\\_C 2D PDF](#)
- [AN16BN0\\_C 3D Inventor](#)
- [AN16BN0\\_C 2D Drawing Xchange](#)
- [AN16BN0\\_C 3D Model Xchange](#)
- [AN16BN0\\_C AutoCAD 2D Footprint](#)
- [Quick Selector - NEMA Contactors](#)

**Certifications:** No Data

**Product compliance:** No Data



