



S9294

12T8U6/LED/22.5-830/DR
 12 watt T8 U-Bend LED; 50000 average rated hours; Medium bi-pin base; 1800 lumens; 3000K



Features

- Direct Replacement - for use on Instant Start and Rapid Start ballasts with no rewiring required*
- Ballast required
- Solid State LED lighting
- High efficacy
- Long life
- 32watt Fluorescent equivalency
- 5 year Limited warranty

S9294

*May not be compatible with all electronic ballasts.

View: [Ballast Compatibility Chart](#)

This item has been discontinued.
 Possible replacement:

- [S9994](#)

Item Number	UPC	Watts	Fluorescent Equivalent	Lamp Shape	Base	ANSI Base	Lamp Code	
S9294	045923092947	12	32W	T8	Medium Bi-Pin	G13	12T8U6/LED/22.5-830/DR	
Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Leg Spacing	Initial Lumens	Average Rated Hours	Kelvin Temp	
Non-Dimmable	White	22.5"	1.00"	6"	1800	50000	3000	
Color	CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant	UL or ETL Listed	Warranty	
Warm White	82	230	12	Box	Yes	Yes	5 Year Limited	
Status				Suggested Substitute				
Discontinued				S9994				



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

